

VISISCOPE® MICROSCOPE ADAPTERS FOR CAMERAS

Camera	VisiCam 3 plus (1/2,7'), VisiCam 5 plus (1/2,5')	VisiCam TC20plus (1/2.5'), VisiCam HDMI5 (1/2.5')	VisiCam HDMI6 (1/2.8'), VisiCam HP (1/2.8')	VisiCam 6 plus (1/1.8'), VisiCam 10 (1/2.3'), VisiCam 16 plus (1/2,33'), VisiCam P6 (1/1.8'), VisiCam MET 5000 (1/1.8'), VisiCam 14 HRS (1/2.3')	VisiCam FL 1400 (1/1.2'), VisiCam PRO 20	VisiCam 20 plus (1')	VisiCam B5 (1/2.5')	VisiCam HE (1/2.8')	VisiCam Wifi 83 (1/2.5')	Tablet TC210 (1/2.5')
VisiScope Model										
BL114, BL124 (binocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Not compatible
BL214, BL224, BL254, BL224 PI (binocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Not compatible
TL224, TL254 (trinocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Included with the camera
BL384 P, BL384 PI, BL384 PH, BL384 PHI (binocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Not compatible
TL384 P, TL384 PI, TL384 PH, TL384 POL, T384 FL, TL384 PHI, TL384 FL, TL384 M (trinocular head)	630-1748 630-1749	630-1749	630-1748	630-1749	630-2946	630-2960	630-1749	630-1748	630-1749	630-1749
BL524 P, BL524 PI, BL524 PH (binocular head)	Included with the camera	630-1749	630-1748	630-2720	630-2606	Included with the camera	630-1749	630-1749	630-1749	630-1749
TL524 P, TL524 PI, TL524 PH (trinocular head)	630-1748	630-1749	630-1748	630-1749	630-2946	630-2960	630-1749	630-1749	630-1749	630-1749
TL534, TL534 PH, TL534 FL (trinocular head)	630-1748 630-1749	630-1749	630-1748	630-1749	630-2946	630-2960	630-1749	630-1748	630-1749	630-1749
TL824 BF, TL824 PH (trinocular head)	630-1748 630-1749	630-1749	630-1748	630-1749	630-2946	630-2960	630-1749	630-1748	630-1749	630-1749
IT415 PH (trinocular head)	630-1748 630-1749	630-1749	630-1748	630-1749	630-2946	630-2960	630-1749	630-1748	630-1749	630-1749
SZB250, STB250 (binocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Not compatible
SZT250 (trinocular head)	630-1792 630-1793	630-1793	630-1792	630-1793	630-3070	630-2960	630-1793	630-1792	630-1793	630-1793
STB150 (binocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Not compatible
SZB350, SZBL350, SZB350 OH (binocular head)	Included with the camera	630-1644	630-2720	630-1644	630-2993	Included with the camera	Included with the camera	630-2720	Included with the camera	Not compatible
SZT350, SZTL350, SZT350 OH (trinocular head)	630-1792 630-1793	630-1793	630-1792	630-1793	630-3070	630-2960	630-1793	630-1792	630-1793	630-1793



630-1748
0.35x focusable C-Mount adapter



630-1792
0.35x focusable C-Mount adapter



630-1644
0.37x C-Mount projection lens



630-2735
Focusable C-mount adapter



630-1749
0.5x focusable C-Mount adapter



630-1793
0.5x focusable C-Mount adapter



630-2720
0.5x C-Mount projection lens



630-2993
0.75x C-Mount projection lens CCD118



630-2946
0.65x focusable C-Mount adapter



630-2960
1x focusable C-Mount adapter



630-2606
1x focusable C-Mount adapter